



[www.ProLux3D.com](http://www.ProLux3D.com)

Vielen Dank für ihren Einkauf

Hutschienenhalterung für Shelly/Fibaro/Rademacher/LoraTap

Material: PETG Kunststoff  
Herstellung aus dem 3D Druck

Die Lieferung erfolgt wie in der Beschreibung erwähnt ohne Finish.  
Ohne Finish bedeutet das die gedruckten Teile direkt aus dem Drucker ohne eine Nachbearbeitung geliefert werden. Eine Nachbearbeitung ist teilweise erforderlich um Produktreste und scharfe Kanten zu entfernen.

Vor der Nutzung bitte Produktreste und scharfe Kanten mit einer Feile ( z.B. Nagelfeile ) entfernen.

Es wird keine Haftung übernommen bei unsachgemäßer Befestigung oder Zweckentfremdung.

#### **Montagehinweis für Hutschienenhalter:**

**Zur Befestigung ( Einfache und Single ) legen sie die obere Nase auf die Hutschiene und klicken sie die untere Nase auf die Hutschiene.**

**Zur Befestigung ( Doppel ) legen sie die untere Nase in die Hutschiene und schieben den Riegel runter auf die Hutschiene.**

Ich möchte meine Artikel stetig verbessern, wenn sie einen Verbesserungsvorschlag haben, teilen sie mir diesen unbedingt mit.

Eigenschaften PETG Kunststoff

Temperaturbeständig -40°C bis +65°C

Brandverhalten UL 94 B1

UV-Beständig

Resistent gegen die meisten Chemikalien ( Desinfizierbar )

PETG Elastizität 5-6%

Physiologisch Unbedenklich ( Lebensmittelecht )

Zu 100% Recyclebar ( Gelbe Tonne )

Formstabil bis +70° ( Wenn sie die Form etwas ändern möchten, vorsichtig mit einem Fön erwärmen und in die gewünschte Form bringen. )

MfG

Lux Metallbau und 3D Druck

U. Lux

Holstenstr. 2

49809 Lingen - Germany

[info@ProLux3D.com](mailto:info@ProLux3D.com)

English:

Thank you for your purchase

DIN rail mount for Shelly/Fibaro/Rademacher/LoraTap

Material: PETG plastic

Production from 3D printing

The delivery takes place as mentioned in the description without finish.

Unfinished means that the printed parts are delivered directly from the printer without any post-processing. Post-processing is sometimes required to remove product residue and sharp edges.

Before use, please remove product residues and sharp edges with an file (e.g. nail file).

No liability is assumed for improper attachment or misuse.

Installation instructions for DIN rail holder:

For attachment (simple and single), place the upper lug on the top-hat rail and click the lower lug on the top-hat rail.

For attachment (double), place the lower lug in the top-hat rail and push the bolt down onto the top-hat rail.

I would like to constantly improve my articles, if you have a suggestion for improvement, please let me know.

Properties PETG plastic

Temperature resistant -40°C to +65°C

Fire behavior UL 94 B1

UV-resistant

Resistant to most chemicals (can be disinfected)

PETG elasticity 5-6%

Physiologically safe (food safe)

100% recyclable (yellow bin)

Dimensionally stable up to +70° (If you want to change the shape, carefully heat it up with a hair dryer and bring it into the desired shape.)

Kind regards

Lux Metallbau und 3D Druck

U. Lux

Holstenstr. 2

49809 Lingen - Germany

[info@ProLux3D.com](mailto:info@ProLux3D.com)